

# SCHOTT® Fiber Optic Image Inverter

## High Resolution Image Inversion



### Night Vision

Image Inverters flip the image 180° minimizing the size and complexity of the night vision eyepiece assembly.

### Performance Characteristics

Fiber optic inverters are used primarily in night vision image intensifier tubes, but these imaging components can be used in any application that requires the correction of an inverted image, while also providing a compact, vacuum tight and rugged package. Fiber optic inverters are manufactured using fiber elements ranging in size from 4 to 25um that are fused together into a coherent imaging array. The billet is then heated and twisted to invert the image 180 degrees from the input surface to the output surface.

### Typical Material Properties

Typical Performance Parameters	Glass Type*		
	24A	24AS	24C
Fiber Size (µm) / Resolution lp/mm**	25/23	25/23	25/23
	10/64	10/64	10/64
	8/72	8/72	6/102
		6/102	4/128
Numerical Aperture	1.0	1.0	1.0
Stray Light Control (EMA)	Yes	Yes	No
Collimated Transmission at 550 nm 30mm Thick (%)	66	66	83
Coefficient of Thermal Expansion (x10 – 7 /°C) 20 – 300°C	68	68	68
Lead Free	No	No	No
Phosphor Compatible	Yes	Yes	Yes

\* Other special glass types available upon customer's request.

\*\* Resolution Measurement performed with an 1951 USAF Resolution Target using diffuse white light illumination. Resolution may vary with other wavelengths.



Version 01.2023

[schott.com](http://schott.com)

SCHOTT AG, Hattenbergstrasse 10, 55122 Mainz, Germany  
Phone: +49 (0) 6131/66-0, [lightingimaging@schott.com](mailto:lightingimaging@schott.com)

**SCHOTT**  
glass made of ideas