

N-SF10 728285.305

$n_d = 1,72828$

$v_d = 28,53$

$n_F - n_C = 0,025524$

$n_e = 1,73430$

$v_e = 28,31$

$n_F - n_C = 0,025941$

Brechzahlen

	λ [nm]	
$n_{2325,4}$	2325,4	1,67981
$n_{1970,1}$	1970,1	1,68597
$n_{1529,6}$	1529,6	1,69308
$n_{1060,0}$	1060,0	1,70217
n_t	1014,0	1,70340
n_s	852,1	1,70891
n_r	706,5	1,71688
n_C	656,3	1,72091
$n_{C'}$	643,8	1,72206
$n_{632,8}$	632,8	1,72314
n_D	589,3	1,72806
n_d	587,6	1,72828
n_e	546,1	1,73430
n_F	486,1	1,74643
$n_{F'}$	480,0	1,74800
n_g	435,8	1,76191
n_h	404,7	1,77578
n_i	365,0	
$n_{334,1}$	334,1	
$n_{312,6}$	312,6	
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Konstanten der Dispersionsformel

B_1	1,621539020
B_2	0,256287842
B_3	1,644475520
C_1	0,01222414570
C_2	0,0595736775
C_3	147,4687930

Konstanten der Formel für dn/dT

D_0	-4,68E-06
D_1	7,41E-09
D_2	-1,89E-11
E_0	9,49E-07
E_1	1,42E-09
λ_{TK} [μm]	0,279

Temperaturkoeffizienten der Lichtbrechung

[°C]	$\Delta n_{rel}/\Delta T$ [$10^{-6}/K$]			$\Delta n_{abs}/\Delta T$ [$10^{-6}/K$]		
	1060,0	e	g	1060,0	e	g
-40/-20	-0,4	1,3	3,4	-2,7	-1,1	1,0
+20/+40	-0,5	1,5	4,1	-2,0	-0,1	2,5
+60/+80	-0,5	1,7	4,6	-1,7	0,5	3,4

Reintransmissionsgrad τ_i

λ [nm]	τ_i [10mm]	τ_i [25mm]
2500	0,850	0,660
2325	0,900	0,760
1970	0,971	0,930
1530	0,994	0,985
1060	0,996	0,990
700	0,993	0,983
660	0,990	0,976
620	0,991	0,977
580	0,991	0,978
546	0,989	0,973
500	0,978	0,950
460	0,963	0,910
436	0,950	0,870
420	0,920	0,820
405	0,870	0,700
400	0,840	0,640
390	0,730	0,450
380	0,530	0,200
370	0,180	
365	0,060	
350		
334		
320		
310		
300		
290		
280		
270		
260		
250		

Farbcode

λ_{80} / λ_5 42/36

Bemerkungen

Relative Teildispersionen P

$P_{s,t}$	0,2160
$P_{C,s}$	0,4701
$P_{d,C}$	0,2888
$P_{e,d}$	0,2359
$P_{g,F}$	0,6066
$P_{i,h}$	

Relative Teildispersionen P'

$P'_{s,t}$	0,2125
$P'_{C',s}$	0,5068
$P'_{d,C'}$	0,2398
$P'_{e,d}$	0,2321
$P'_{g,F'}$	0,5365
$P'_{i,h}$	

Abweichung rel. Teildisp.

ΔP von der "Normalgeraden"

$\Delta P_{C,t}$	0,0057
$\Delta P_{C,s}$	0,0007
$\Delta P_{F,e}$	0,0019
$\Delta P_{g,F}$	0,0108
$\Delta P_{i,g}$	

Chemische Eigenschaften

CR	1
FR	0
SR	1
AR	1
PR	1

Sonstige Eigenschaften

$\alpha_{-30/+70^\circ\text{C}}$ [$10^{-6}/K$]	9,4
$\alpha_{+20/+300^\circ\text{C}}$ [$10^{-6}/K$]	10,8
T_g [°C]	559
T_{10}^{13} [°C]	549
$T_{10}^{7,6}$ [°C]	652
c_p [J/(g·K)]	0,740
λ [W/(m·K)]	0,960
ρ [g/cm ³]	3,05
E [10^3 N/mm ²]	87
μ	0,252
K [10^{-6} mm ² /N]	2,92
HK _{0,1/20}	540
HG	5