

Pioneering. Responsibly. Together. These attributes have characterized SCHOTT, manufacturer of special glass, glass-ceramics and other innovative materials, for over 130 years. As #glasslovers and inventor of special glass, we are reliable partners for high-tech industries to enable new market launches and applications. Our goal is to become climate neutral by 2030.

SCHOTT Electronic Packaging is a world-leading supplier of hermetically-sealed components for the reliable, long-term protection of sensitive electronic devices. Our products enable electronics in oil & gas equipment to function reliably deep underwater and underground. Drawing on more than 75 years of manufacturing expertise, SCHOTT components are designed to withstand the challenging operating conditions found in oil & gas application environments of 205°C temperatures and pressure levels of 20,000 PSI. This handbook provides helpful information on the advantages of Eternaloc® Subsea Connectors and Feedthroughs.


### Made to survive the conditions of hell on earth.








**Exploration connectors** 



MCM housings





# SCHOTT Eternaloc® Subsea Connectors & Feedthroughs Years of maintenance-free robustness above 20,000 PSI




### **Product Information**

Eternaloc® connectors are maintenance-free, customizable barriers that are hermetically sealed and remain leak-tight, even after years of use. They offer long-term durable protection of subsea tree components, such as wellhead pressure sensors, in high temperature, high pressure conditions.




#### **Advantages**

• Long-term, maintenance-free durability can prevent costly component replacements: Decades of proven maintenance-free performance in harsh environment applications, including nuclear power plants, LNG and hydrogen gas cooling.




- Design pressure: 20,000 PSI - Burst pressure: 50,000 PSI



Simplifying your processes with less welds:
 We can offer complete subsea connector assemblies.



- Large variety of specialty glass materials and metals available, including fiber optic glass.
- Dimensions up to 600 mm (23 inches) diameter, 500 mm (20 inches) height and 250 kg (550 lb) weight.
- Electrical performance up to 13,800V, 1500A; coax, triax and fiber optic connections available.
- Additional insulating materials available, such as PEEK, PTFE, shrinking tubes and potting materials.





### **Multi-Chip Module Housings**


## High temperature- and shock-resistant packaging for exploration and subsea electronics

#### **Product Information**

Hermetic multi-chip module (MCM) housings are used for protective packaging of sensitive measurement and control electronics in harsh environment conditions. Simultaneously, built-in Glass-or Ceramic-to-Metal Sealed Connectors enable power and signal transmission (electrical and optical) into and out of the package.

### **Advantages**

- High-temperature glass or ceramic materials:
   Suitable for working environments of 175°C / 347°F and above.
- Shock and vibration resistance:
   Designed to endure extreme pressure and vibrations in harsh working environments.






Multi-Chip Modules (MCM) with Kovar® and Ti packages



High-power amplifiers with heat sink



High-pressure feedthroughs



High-power/high-frequency surface mount package with heat sink



# SCHOTT Eternaloc® Connectors for Oil Exploration Superior HPHT robustness above 35,000 PSI

#### **Product Information**

SCHOTT has developed customizable Eternaloc® connectors for use in high pressure, high temperature oil & gas exploration environments. Eternaloc connectors are designed to support safe and reliable transmission of valuable data and information provided by sensors in Wireline, MWD and LWD applications.

### **Advantages**

- **35,000 PSI and above:** Robust glass-to-metal seals maintain integrity in some of the harshest environments on earth with 35KSI design pressure and 50KSI burst pressure resistance.
- Superior pressure resistance and insulation resistance under extreme conditions:
   ≥ 10GΩ with our high-temperature sealing glasses, higher IR can be achieved at 500°F / 260°C in some circumstances.
- Extreme temperature resistance: Eternaloc® connectors are designed to withstand temperatures in excess of 500°F / 260°C.
- Fully customizable: Single and multi-pin, male/female connections, and custom materials flexible design and sampling for a variety of applications.













### Specialty glass seals – The secret to success

### Thermoplastic

The extreme conditions in drilling applications are prohibitive for lesser-quality materials. Connectors using thermoplastic seals are prone to deformation from creepage, leading to an increased risk of seal compromise.

### **SCHOTT** glass-sealing

Connectors sealed with specialty glass maintain integrity even at 35KSI / 260°C (500°F) thanks to:

- Inorganic, non-aging material
- Resistance to extreme temperatures



Glass seals maintain integrity

### **SCHOTT AG**

Christoph-Dorner-Straße 29 84028 Landshut Germany Phone +49 (0) 871 826 0 ep.info@schott.com www.schott.com/epackaging





Information provided herein is general information and may vary depending on the circumstances. SCHOTT takes no responsibility for the accuracy of this information or any reliance thereon. Despite the fact that all reasonable care was taken in presenting and keeping this information up to date, SCHOTT neither accepts any legal responsibilities nor guarantees the completeness, accuracy or up-to-dateness of the information presented here. Any information provided herein is not intended to be, and should not be construed as, any warranty or guarantee. Date issued: February 2021.