



SCHOTT Termofrost® CRS: Insulated doors for chiller and freezer cold rooms.

The complete range for your cold rooms requirements

SCHOTT Termofrost® CRS Classic: glass door systems for cold rooms

Product description

This timeless and functional glass door system displays chilled and frozen goods stored in cold rooms. Our large selection of door systems provides the flexibility for realising various reach-in or walk-in solutions in many configurations and sizes.

Meat, dairy products, ice cream, frozen vegetables or flowers are perfectly visible through the door while the required temperature for the stored goods is maintained. Good insulation properties of the doors support energy efficiency of cold rooms in petrol stations, cash & carry markets and other food retail stores.

A flexible shelving system complements this display door range: chilled and frozen food can be presented in a well arranged, attractive manner.

Take advantage of the benefits

- Large variety of door variants
- Perfectly insulated door for chiller and freezer presentation
- Condensation free view
- Robust frame and door construction
- Hold open function for easy refilling of the shelves



Universal installation possibilities

Technical specifications

		SCHOTT Termofrost® CRS Classic
Description	Type	Swing door
	Application	Cold rooms or refrigeration cells
	Temperature range	<ul style="list-style-type: none"> ▪ Chilled storage +2° to +8 °C ▪ Frozen storage -25° to -18 °C
System configuration	Number of doors per frame	1-5
	Door	Right hinged
Glass	Chiller applications	Passive double glazing
	Freezer applications	<ul style="list-style-type: none"> ▪ Heated triple glazing ▪ Passive triple glazing with anti-fog coating
Standard Dimension (mm)	Door height	T = Normal height 1600 mm S = Super height 1800 mm SE = Super Extended height 2031 mm R = Roll-In height 1900 mm W = Walk-In height 2031 mm
	Door width	66 = 660 mm 76 = 760 mm 90 = 900 mm
Handle		<ul style="list-style-type: none"> ▪ Bowed handle ▪ Full length handle (on request)
Door opening features		<ul style="list-style-type: none"> ▪ Selfclosing ▪ Door stop ▪ Hold open
Light		<ul style="list-style-type: none"> ▪ LED modules
U-value/sqmK		0.8-1.7 W/sqmK (depending on configuration)
Colors	Door rail and outer frame	<ul style="list-style-type: none"> ▪ Nature anodized ▪ Black anodized
Accessories	Shelving system	Designed to fit any door configuration

Please contact your local sales representative for available configurations.