





Where does your next mission take you?

With hermetic glass-to-metal sealing

Hermetic packages in space

"You don't get a second chance in space" – Space missions do not allow for compromise. With hermetic microelectronic packages from SCHOTT, mission-critical microelectronics can be protected even in the harshest and most challenging environments.


Made for space – properties of our hermetic packages



Lightweight
Reduces weight to a minimum




Heat resistant
Withstands temperatures of up to 1,000 °C



Radiation hardened
Protects against space radiation

SCHOTT

Components of our multifunctional lightweight package




Made for you – benefits of working with SCHOTT



Customized
according to your specifications



Reliable
protection in harsh environments



Complex
structures and designs

Space applications

- DC/DC converter
- Power amplifier
- Power over fiber
- Microwave electronics
- Radar electronics
- Gyroscopes
- Photosensing (Photodiodes, APDs etc.)
- CCD & CMOS imaging
- UV/VIS/IR applications
- LiDAR

[schott.com/hybrid](https://www.schott.com/hybrid)

SCHOTT AG, Prof.-Schott-Strasse 1, 84034 Landshut, Germany
Phone +49 (0) 871/826-283, georg.mittermeier@schott.com

SCHOTT