SCHOTT RealView® – High Index Glass Wafer for Augmented Reality



Product Information

The still unimaginable cosmos of Augmented Reality experience is expected to change our everyday life – during work, during leisure time, the way we communicate.

High index glass wafer are a key component in the optical system influencing the visual user experience, such as Field-of-View (FoV) and image quality.

Our customers have in SCHOTT a strong partner, committed to innovation, high quality and reliable mass production.


Augmented Reality device requirement	Customizeable properties of SCHOTT RealView®	Typical properties
Field of view	Refractive index	1.5, 1.6, 1.7, 1.8, 1.9, 2.0
Image quality (resolution, contrast, brightness,)	High transmission	Optical glass grade
	Low birefringence	No polarization dependency of waveguide
	High homogeneity	Optical glass grade
	Flatness and thickness homogeneity	TTV < 0.8 μm
		Local slope < 0.16 arcmin
		Wedge < 0.03 arcmin
		Warp* uncoated / coated $<$ 20 μ m / $<$ 50 μ m
		BOW* uncoated/coated < 10 μm/< 20 μm
	Roughness uncoated/coated	$R_{\rm a} < 1.0 \rm nm / 1.5 nm$
	Anti reflective coating	Tailormade to customer requirements
	Cosmetic	40/20 scratch/dig
Form factor (light, weight, thin)	Low wafer thickness	≥ 0.3 mm
	Specific weight	Depending on glass type
	Glass strength and stability	Compatible with automated wafer handling equipment
Mass manufacturing process	Wafer size	150 mm, 200 mm, 300 mm
	High volume processing and quality control	Full metrology capabilitites in mass production environment. Statistical process control established.

All data can be adapted on request. Please contact your SCHOTT representative.



^{*}depending on wafer size, thickness and coating

SCHOTT RealView® – High Index Glass Wafer for Augmented Reality






TTV Metrology

Coating Chamber

With our portfolio of more than 120 optical glasses, SCHOTT is an expert in mass manufacturing optical materials with properties tailored for our customer's applications. Our manufacturing capabilities cover raw glass melting, wafer manufacturing, optical coatings fulfilling the tightest specifications of the industry.

Our team is keen to learn more about your needs!



SCHOTT AG
Hattenbergstrasse 10
55122 Mainz, Germany
Phone +49 (0)6131/66-1695
real.view@schott.com

SCHOTT glass made of ideas

/ersion December 2021 | SCHOTT reserves the right to make specification changes in this product flyer without notice