


# SCHOTT NEXTREMA® tinted

## Black design and excellent heat output

NEXTREMA® tinted delivers a black design that fits into basically every environment, hiding the heating elements when switched off. When the heater is powered on, the excellent transmission for radiant heat ensures a high heat output at minimal glare.


### Material benefits

- High transmission in the IR-A and IR-B range
- Black design
- Hides the heating element when switched off



## Overlay of NEXTREMA® transmission with heating element emission spectra

Transmission [%]



### NEXTREMA® transmission curves

- NEXTREMA® tinted  
Thickness: approx. 3.2 mm
- NEXTREMA® tinted  
Thickness: approx. 4 mm
- NEXTREMA® tinted  
Thickness: approx. 6 mm

\*Transmission graphs are based on data from individual measurements. These specified transmission values refer to glass-ceramic material, both sides flat and polished. Deviations may result from the manufacturing process.


# SCHOTT NEXTREMA® tinted

Appearance in combination with different heating elements

## Short wave emitter



NEXTREMA® tinted | Short wave emitter – by day




NEXTREMA® tinted | Short wave emitter – by night

## Carbon emitter



NEXTREMA® tinted | Carbon emitter – by day




NEXTREMA® tinted | Carbon emitter – by night

## Medium wave emitter



NEXTREMA® tinted | Medium wave emitter – by day



NEXTREMA® tinted | Medium wave emitter – by night

[schott.com/nextrema](https://schott.com/nextrema)

SCHOTT North America, Inc., 5530 Shepherdsville Road, Louisville, KY 40228, USA  
[info.robax@schott.com](mailto:info.robax@schott.com)

SCHOTT