

N-LASF46B 904313.451

$n_d = 1,90366$

$v_d = 31,32$

$n_F - n_C = 0,028852$

$n_e = 1,91048$

$v_e = 31,09$

$n_F - n_C = 0,029289$

Brechzahlen

	λ [nm]	
$n_{2325,4}$	2325,4	1,84657
$n_{1970,1}$	1970,1	1,85418
$n_{1529,6}$	1529,6	1,86283
$n_{1060,0}$	1060,0	1,87362
n_t	1014,0	1,87505
n_s	852,1	1,88146
n_r	706,5	1,89065
n_C	656,3	1,89526
$n_{C'}$	643,8	1,89657
$n_{632,8}$	632,8	1,89781
n_D	589,3	1,90341
n_d	587,6	1,90366
n_e	546,1	1,91048
n_F	486,1	1,92411
$n_{F'}$	480,0	1,92586
n_g	435,8	1,94130
n_h	404,7	1,95647
n_i	365,0	
$n_{334,1}$	334,1	
$n_{312,6}$	312,6	
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Konstanten der Dispersionsformel

B_1	2,179889220
B_2	0,306495184
B_3	1,568824370
C_1	0,01258053840
C_2	0,0567191367
C_3	105,3165380

Konstanten der Formel für dn/dT

D_0	5,98E-06
D_1	1,30E-08
D_2	-3,50E-12
E_0	9,13E-07
E_1	1,24E-09
λ_{TK} [μm]	0,267

Temperaturkoeffizienten der Lichtbrechung

[°C]	$\Delta n_{rel}/\Delta T$ [$10^{-6}/K$]			$\Delta n_{abs}/\Delta T$ [$10^{-6}/K$]		
	1060,0	e	g	1060,0	e	g
-40/-20	6,1	8,2	10,7	3,6	5,6	8,1
+20/+40	6,4	8,9	11,8	4,8	7,2	10,1
+60/+80	6,8	9,5	12,7	5,5	8,2	11,4

Reintransmissionsgrad τ_i

λ [nm]	τ_i [10mm]	τ_i [25mm]
2500	0,560	0,230
2325	0,790	0,550
1970	0,954	0,890
1530	0,991	0,977
1060	0,998	0,996
700	0,996	0,989
660	0,993	0,983
620	0,992	0,980
580	0,991	0,978
546	0,989	0,972
500	0,977	0,940
460	0,954	0,890
436	0,930	0,840
420	0,900	0,770
405	0,850	0,660
400	0,820	0,600
390	0,710	0,420
380	0,500	0,180
370	0,180	0,010
365	0,050	0,000
350		
334		
320		
310		
300		
290		
280		
270		
260		
250		

Farbcode

λ_{70} / λ_{50} 41/37

Bemerkungen

zum Blankpressen geeignet

Relative Teildispersionen P

$P_{s,t}$	0,2222
$P_{C,s}$	0,4783
$P_{d,C}$	0,2911
$P_{e,d}$	0,2364
$P_{g,F}$	0,5956
$P_{i,h}$	

Relative Teildispersionen P'

$P'_{s,t}$	0,2189
$P'_{C',s}$	0,5160
$P'_{d,C'}$	0,2419
$P'_{e,d}$	0,2329
$P'_{g,F'}$	0,5270
$P'_{i,h}$	

Abweichung rel. Teildisp.

ΔP von der "Normalgeraden"

$\Delta P_{C,t}$	0,0069
$\Delta P_{C,s}$	0,0024
$\Delta P_{F,e}$	0,0006
$\Delta P_{g,F}$	0,0045
$\Delta P_{i,g}$	

Chemische Eigenschaften

CR	1
FR	0
SR	3,3
AR	1
PR	1
SR-J	2
WR-J	1

Sonstige Eigenschaften

$\alpha_{-30/+70^\circ\text{C}}$ [$10^{-6}/K$]	6,0
$\alpha_{+20/+300^\circ\text{C}}$ [$10^{-6}/K$]	7,1
T_g [°C]	611
T_{10}^{13} [°C]	613
$T_{10}^{7,6}$ [°C]	703
c_p [J/(g·K)]	0,550
λ [W/(m·K)]	0,880
AT [°C]	649
ρ [g/cm ³]	4,51
E [10 ³ N/mm ²]	121
μ	0,303
K [10 ⁻⁶ mm ² /N]	1,87
HK _{0,1/20}	712
Abrasion Aa	55