

# BOROFLOAT® 33 – Optical Properties

The sum of its properties is what makes it unique.

BOROFLOAT® 33 from Germany is the world's first floated borosilicate flat glass. It combines superior quality and excellent flatness with outstanding thermal, optical, chemical and mechanical features. The chemical composition and physical properties of BOROFLOAT® 33 are in accordance with DIN ISO 3585 and DIN EN 1748 T1. Rediscover BOROFLOAT® 33 and experience the infinite potential of our most versatile material platform. BOROFLOAT® – Inspiration through Quality.



Optical wheel made of BOROFLOAT® 33.

## Key benefits:


### Exceptionally high transparency

- High transparency in visible and near IR & UV range of wavelengths
- Outstanding visual quality and optical clarity
- Low inherent fluorescence and solarisation tendency

## Dispersion

|           | $n_{248.3}^*$ | $n_{296.7}$ | $n_i$ | $n_g$ | $n_F$ | $n_e$ | $n_d$ | $n_{632.8}$ | $n_{C'}$ | $n_s$ | $n_l$  | $n_{1529.6}$ |
|-----------|---------------|-------------|-------|-------|-------|-------|-------|-------------|----------|-------|--------|--------------|
| $\lambda$ | 248.3         | 296.7       | 365.0 | 435.8 | 480.0 | 546.1 | 587.6 | 632.8       | 643.8    | 852.1 | 1014.0 | 1529.6       |
| $n$       | 1.525         | 1.504       | 1.489 | 1.480 | 1.477 | 1.473 | 1.471 | 1.470       | 1.470    | 1.465 | 1.463  | 1.456        |


\* calculated value done by extrapolation of the dispersion curve




| Optical data                                       |  |
|--|--|
| Abbe number ( $v_e = (n_e - 1) / (n_F - n_{C'})$ ) | 65.41  |
| Refractive index ( $n_d$ )                         | 1.471  |
| Dispersion ( $n_F - n_{C'}$ )                      | $71.4 \times 10^{-4}$                            |
| Stress-optical coefficient (K)                     | $4.0 \times 10^{-6} \text{ mm}^2 \text{ N}^{-1}$ |

Reference values, not guaranteed values.

## Transmittance at 250 – 2800 nm




## Transmittance at 250 – 400 nm




## Transmittance at 250 – 800 nm – Comparison BOROFLOAT® 33 vs. different glass materials

For applications requiring thin glass substrates



For applications requiring thicker glass substrates




### Radiation of Light

Glasses transmit a certain amount of radiation energy. The incident radiation energy is reduced by absorption and reflection (up to 8 %)\*.

The sum of reflection, transmittance and absorption is 100 %.

The glass composition, the network structure and the glass thickness as well as the wavelength of the radiation have a direct influence on the transmitted intensity of radiation energy.

\* Floated glass surfaces show typically around 8 % reflection losses.



### Ultraviolet transmittance $\tau_{UV}$ and light transmittance $\tau_V$

The ultraviolet transmittance  $\tau_{UV}$  and light transmittance  $\tau_V$  are calculated values according to the methods described in DIN EN 410:2011-04. This European Standard describes methods of determining the luminous and solar characteristics of glazing in buildings.

|                          |    | BOROFLOAT® 33 |      |      |      |      |      |      | low iron soda-lime float glass |      | alkali-free flat glass * |
|--------------------------|----|---------------|------|------|------|------|------|------|--------------------------------|------|--------------------------|
| Glass thickness          | mm | 0.7           | 1.1  | 3.3  | 3.8  | 5.0  | 9.0  | 11.0 | 3.3                            | 5    | 1.1                      |
| $\tau_{UV}$ (280–380 nm) | %  | 91.8          | 91.6 | 90.5 | 89.9 | 89.3 | 85.9 | 84.9 | 83.7                           | 80.0 | 84.1                     |
| $\tau_V$ (380–780 nm)    | %  | 92.8          | 92.7 | 92.6 | 92.5 | 92.5 | 92.0 | 91.9 | 91.5                           | 91.0 | 92.3                     |

\* drawn TFT-LCD glass

All values listed on the data sheet are not guaranteed reference values.

SCHOTT Technical Glass Solutions GmbH  
 Otto-Schott-Strasse 13, 07745 Jena  
 Germany  
 Telefon +49 (0) 36 41/681-46 86  
 Telefax +49 (0) 36 41/28 88-92 41

info.borofloat@schott.com  
 www.schott.com/borofloat

**SCHOTT**  
 glass made of ideas