

N-LASF41 835431.485

$n_d = 1,83501$

$v_d = 43,13$

$n_F - n_C = 0,019361$

$n_e = 1,83961$

$v_e = 42,88$

$n_F - n_C = 0,019578$

Brechzahlen

	λ [nm]	
$n_{2325,4}$	2325,4	1,78859
$n_{1970,1}$	1970,1	1,79608
$n_{1529,6}$	1529,6	1,80423
$n_{1060,0}$	1060,0	1,81338
n_t	1014,0	1,81450
n_s	852,1	1,81936
n_r	706,5	1,82599
n_C	656,3	1,82923
$n_{C'}$	643,8	1,83014
$n_{632,8}$	632,8	1,83100
n_D	589,3	1,83484
n_d	587,6	1,83501
n_e	546,1	1,83961
n_F	486,1	1,84859
$n_{F'}$	480,0	1,84972
n_g	435,8	1,85949
n_h	404,7	1,86872
n_i	365,0	1,88486
$n_{334,1}$	334,1	
$n_{312,6}$	312,6	
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Konstanten der Dispersionsformel

B_1	1,863483310
B_2	0,413307255
B_3	1,357848150
C_1	0,00910368219
C_2	0,0339247268
C_3	93,3580595

Konstanten der Formel für dn/dT

D_0	3,03E-06
D_1	1,04E-08
D_2	-1,30E-11
E_0	6,62E-07
E_1	7,82E-10
λ_{TK} [μm]	0,209

Temperaturkoeffizienten der Lichtbrechung

[°C]	$\Delta n_{rel}/\Delta T$ [$10^{-6}/K$]			$\Delta n_{abs}/\Delta T$ [$10^{-6}/K$]		
	1060,0	e	g	1060,0	e	g
-40/-20	4,0	5,2	6,4	1,5	2,7	3,9
+20/+40	4,0	5,4	6,8	2,4	3,8	5,2
+60/+80	4,2	5,7	7,2	2,9	4,5	6,0

Reintransmissionsgrad τ_i

λ [nm]	τ_i [10mm]	τ_i [25mm]
2500	0,480	0,160
2325	0,760	0,510
1970	0,950	0,880
1530	0,993	0,983
1060	0,998	0,995
700	0,998	0,995
660	0,998	0,994
620	0,997	0,993
580	0,998	0,994
546	0,997	0,993
500	0,994	0,984
460	0,985	0,962
436	0,976	0,940
420	0,967	0,920
405	0,954	0,890
400	0,950	0,880
390	0,930	0,830
380	0,890	0,750
370	0,830	0,630
365	0,790	0,550
350	0,590	0,270
334	0,290	0,040
320	0,040	
310		
300		
290		
280		
270		
260		
250		

Farbcode

λ_{70}/λ_{5} 37/32

Bemerkungen

Relative Teildispersionen P

$P_{s,t}$	0,2508
$P_{C,s}$	0,5098
$P_{d,C}$	0,2986
$P_{e,d}$	0,2378
$P_{g,F}$	0,5629
$P_{i,h}$	0,8338

Relative Teildispersionen P'

$P'_{s,t}$	0,2480
$P'_{C',s}$	0,5507
$P'_{d,C'}$	0,2487
$P'_{e,d}$	0,2351
$P'_{g,F'}$	0,4989
$P'_{i,h}$	0,8245

Abweichung rel. Teildisp.

ΔP von der "Normalgeraden"

$\Delta P_{C,t}$	0,0110
$\Delta P_{C,s}$	0,0063
$\Delta P_{F,e}$	-0,0021
$\Delta P_{g,F}$	-0,0083
$\Delta P_{i,g}$	-0,0520

Chemische Eigenschaften

CR	1
FR	1
SR	4
AR	1
PR	1

Sonstige Eigenschaften

$\alpha_{-30/+70^\circ\text{C}}$ [$10^{-6}/K$]	6,2
$\alpha_{+20/+300^\circ\text{C}}$ [$10^{-6}/K$]	7,3
T_g [°C]	651
T_{10}^{13} [°C]	658
$T_{10}^{7,6}$ [°C]	739
c_p [J/(g·K)]	0,490
λ [W/(m·K)]	0,790
ρ [g/cm ³]	4,85
E [10^3 N/mm ²]	124
μ	0,294
K [10^{-6} mm ² /N]	1,57
HK _{0,1/20}	760
HG	2