

N-LASF45 801350.363

$n_d = 1.80107$
 $n_e = 1.80650$

$v_d = 34.97$
 $v_e = 34.72$

$n_F - n_C = 0.022905$
 $n_{F'} - n_{C'} = 0.023227$

Refractive Indices		
	λ [nm]	
$n_{2325.4}$	2325.4	1.75487
$n_{1970.1}$	1970.1	1.76104
$n_{1529.6}$	1529.6	1.76809
$n_{1060.0}$	1060.0	1.77689
n_t	1014.0	1.77805
n_s	852.1	1.78325
n_r	706.5	1.79066
n_C	656.3	1.79436
$n_{C'}$	643.8	1.79541
$n_{632.8}$	632.8	1.79640
n_D	589.3	1.80087
n_d	587.6	1.80107
n_e	546.1	1.80650
n_F	486.1	1.81726
$n_{F'}$	480.0	1.81864
n_g	435.8	1.83068
n_h	404.7	1.84237
n_i	365.0	
$n_{334.1}$	334.1	
$n_{312.6}$	312.6	
$n_{296.7}$	296.7	
$n_{280.4}$	280.4	
$n_{248.3}$	248.3	

Constants of Dispersion Formula	
B_1	1.871401980
B_2	0.267777879
B_3	1.730300080
C_1	0.011217192
C_2	0.0505134972
C_3	147.10650500

Constants of Formula for dn/dT	
D_0	2.78E-06
D_1	8.73E-09
D_2	-2.65E-11
E_0	8.24E-07
E_1	1.15E-09
λ_{TK} [μm]	0.255

Temperature Coefficients of the Refractive Index						
[°C]	$\Delta n_{rel}/\Delta T$ [$10^{-6}/K$]			$\Delta n_{abs}/\Delta T$ [$10^{-6}/K$]		
	1060.0	e	g	1060.0	e	g
-40/-20	3.8	5.4	7.3	1.4	3.0	4.7
+20/+40	3.8	5.7	7.9	2.3	4.1	6.2
+60/+80	3.8	5.9	8.3	2.6	4.7	7.0

Internal Transmittance τ_i		
λ [nm]	τ_i [10mm]	τ_i [25mm]
2500	0.810	0.580
2325	0.880	0.720
1970	0.972	0.930
1530	0.995	0.988
1060	0.999	0.997
700	0.996	0.990
660	0.995	0.987
620	0.994	0.984
580	0.994	0.986
546	0.993	0.982
500	0.983	0.958
460	0.965	0.920
436	0.950	0.870
420	0.920	0.820
405	0.880	0.720
400	0.860	0.680
390	0.790	0.550
380	0.670	0.370
370	0.480	0.150
365	0.340	0.060
350	0.010	
334		
320		
310		
300		
290		
280		
270		
260		
250		

Color Code	
$\lambda_{80} / \lambda_{5}$	44/35

Remarks

Relative Partial Dispersion P	
$P_{s,t}$	0.2268
$P_{C,s}$	0.4849
$P_{d,C}$	0.2930
$P_{e,d}$	0.2368
$P_{g,F}$	0.5859
$P_{i,h}$	
Relative Partial Dispersion P'	
$P'_{s,t}$	0.2237
$P'_{C,s}$	0.5235
$P'_{d,C'}$	0.2437
$P'_{e,d}$	0.2336
$P'_{g,F'}$	0.5186
$P'_{i,h}$	

Deviation of Rel. Partial Disp. ΔP from the normal line	
$\Delta P_{C,t}$	0.0009
$\Delta P_{C,s}$	0.0005
$\Delta P_{F,e}$	0.0001
$\Delta P_{g,F}$	0.0009
$\Delta P_{i,g}$	

Chemical Properties	
CR	1
FR	0
SR	3.2
AR	1
PR	1

Other Properties	
$\alpha_{-30/+70^\circ C}$ [$10^{-6}/K$]	7.4
$\alpha_{+20/+300^\circ C}$ [$10^{-6}/K$]	8.6
T_g [°C]	647
T_{10}^{13} [°C]	652
$T_{10}^{7.6}$ [°C]	773
c_p [J/(g*K)]	0.660
λ [W/(m*K)]	1.020
ρ [g/cm ³]	3.63
E [10^3 N/mm ²]	116
μ	0.281
K [10^{-6} mm ² /N]	2.01
HK _{0.1/20}	630
HG	3