

GOETHEGLAS RESTOVER® TIKANA®

Glass for restoration



SCHOTT



For the Mirador "El Palmeral" at Vitoria-Gasteiz City Hall, SCHOTT RESTOVER® plus and colored glass in "Florentine" and "Muranese" patterns were selected to faithfully preserve the historic appearance.

Mirador "El Palmeral", Vitoria-Gasteiz, Spain

Photo: © Donca fotografia

Cover: The windows of the German Historical Museum located in a former arsenal in Berlin are special energy-efficient windows including RESTOVER® glass for restoration.

Photo: Gallandi Klönk

SCHOTT's glasses for restoration are the best choice for the faithful restoration of historical buildings from various eras – mimicking the appearance of the original glazing materials – GOETHEGLAS for buildings from the 18th and 19th centuries, RESTOVER® glass for buildings dating from the early 1900s and TIKANA® glass for buildings from the classical modern period – these glasses also meet any number of contemporary needs because of the wide variety of processing options available, from UV protection to thermal insulation.




TIKANA® was used to authentically glaze the historical bands of windows in the former Schocken department store in Chemnitz.

Schocken department store, Chemnitz, Germany

Photos: Roland Halbe

Accurate in style and true to the times. Historical in form, innovative in function

Restoring historical monuments is a delicate task in which every aesthetic nuance is important. SCHOTT's glasses for restoration provide the wide range of materials that architects need to do the job right. Manufactured using the traditional Fourcault process, the look of the glass is based on historical window glasses from different eras.



Production process

The traditional Fourcault process vertically draws glass from a liquid melt upwards through a nozzle and into a drawing shaft. At the end of the shaft, the glass is cut to size.

SCHOTT restoration glass exhibit striations typical for this production process. The glass also has varying degrees of waviness depending on the product.

These dynamic surfaces make the glass the ideal choice for faithfully restoring windows and doors in historical buildings and monuments of different eras.




SCHOTT glass for restoration

- GOETHEGLAS for buildings from the 18th and 19th centuries
- RESTOVER® glass for buildings from the early 1900s
- TIKANA® glass for buildings from the classical modern period
- ETA certification according to standards EN 12150-2, EN 14179-2, EN 14449 and EN 1279-5
- Many processing options to make standard-compliant building products (e.g. as toughened safety glass, laminated safety glass, laminated glass and insulating glass units)

TIKANA® restoration glass was used to renovate the Van de Velde Building of the Bauhaus-University in Weimar.

Photo: © SCHOTT



GOETHEGLAS

GOETHEGLAS is a colorless, drawn glass with the irregular surface characteristic of window glass common to the 18th and 19th centuries. It can also be used to protect precious, leaded glazing from the elements and other adverse environmental conditions.

Orangery Schwerin Castle, Schwerin, Germany

Photo: © SCHOTT




RESTOVER®

RESTOVER® resembles the window glass manufactured at the turn of the century. Its minimal thickness makes it easy to install in historical window frames and fittings.

While the surface of RESTOVER® light glass is slightly less irregular, RESTOVER® plus glass has a much more irregular surface structure and resembles mouth-blown glass.

Château de l'Aile, Vevey, Switzerland

Photo: Vogel Fensterbauer AG, Goldach, Switzerland



TIKANA®

TIKANA® glass is particularly suited for buildings dating from the Bauhaus style. Its slightly irregular surface harmonizes with buildings from the classical modern period. Like the other SCHOTT restoration glasses, TIKANA® glass offers every opportunity to link historical charm with modern physical building properties.

Maggi-Areal, Kempthal, Switzerland

Photo: Carsten Costard





At the Forchtenberg Mittelmühle, SCHOTT has contributed to the authentic restoration of the building, which has been classified as a historical monument, by supplying RESTOVER® and RESTOVER® light glass for restoration.

Photo: Carsten Costard

SCHOTT glass for restoration

For monument authenticity in step with the times

SCHOTT enhances restoration glazing by integrating proven modern solutions, such as heat insulation-, sun- and UV-protection, secure overhead mounting, burglar resistance, soundprotection, which were unknown at the time of original construction.

Elements of these solutions include coatings and films, inert gas fillings between the window panes and a number of different spacers for insulating glass units, colored or otherwise. For example, an assembly made of TIKANA® glass provides heat insulation and sun protection without detracting from the appearance of the Van de Velde Building at the Bauhaus-University.

Please contact us.

schott.com

SCHOTT North America, Inc., 5530 Shepherdsville Road, Louisville, KY 40228, USA
Phone +1 (502) 657-4417, info.architecture@us.schott.com

Left: Bauhaus-University Weimar – the “Brendelsche Atelier”
using SCHOTT RESTOVER® laminated glass

Photo: © SCHOTT

schott.com

SCHOTT North America, Inc., 5530 Shepherdsville Road, Louisville, KY 40228, USA
Phone +1 (502) 657-4417, info.architecture@us.schott.com

SCHOTT Restoration glass GOETHEGLAS, RESTOVER®, TIKANA®

Technical data sheet

Production and usage

SCHOTT restoration glass

- is created specifically as glazing that corresponds to the historical epoch of a building.
- offers the typical surface characteristics of glass from different historical epochs while also capable of being processed as state-of-the-art insulating and laminated glass.
- is produced using the traditional Fourcault process. The glass is drawn vertically upwards from a liquid melt through a nozzle into a drawing shaft. At the end of the drawing shaft, the glass is cut to sheet size.
- has the striations typical for the manufacturing process. The glass also has varying degrees of waviness depending on the product.
- is the right choice for the faithful restoration of windows and doors in historical buildings and monuments from different epochs.
- is also suitable for glazing historical display cases and furniture as well as historical mirrors.

Processing


1. Are there specifications and structural approvals for SCHOTT restoration glass?

The physical, chemical and technical properties of all SCHOTT restoration glass variants are described in specifications. In addition, all SCHOTT restoration glass has European Technical Assessment ETA-12/0159 from the German Institute for Construction Technology (DIBT), i.e. depending on the glass thickness, it can be processed into standard building products such as toughened safety glass, laminated safety glass and insulating glass.

2. What needs to be considered when cutting the glass?

Due to a possibly higher residual cooling stress and larger distortions than with floated glass, cutting must be carried out with an expansion cut while taking into account specific cutting wheel angles and cutting pressures.

Fourcault process



3. Processing options

- Use of standard PVB films for laminated glass
- Use of thicker films to compensate for thickness fluctuations
- Use of special UV or IR filter films to meet increased light requirements
- Use of sound insulation films to reduce noise pollution in buildings
- Outer pane of insulating glass available as restoration glass
- Use of sun protection layers
- Option to produce insulating glass with an overall thickness of approx. 10 mm

SCHOTT Restoration glass GOETHEGLAS, RESTOVER®, TIKANA®

Technical data sheet

Glass type	Thickness* mm	Thickness tolerance mm	Standard dimensions* mm x mm
GOETHEGLAS	4.5	± 0.50	2,100 x 1,500
			2,400 x 1,500
			2,700 x 1,500
RESTOVER®	2.0	± 0.25	1,600 x 1,400
			2,100 x 1,400
	2.75	± 0.25	1,000 x 1,500
			1,600 x 1,500
			2,400 x 1,500
	4.0	± 0.25	2,100 x 1,500
			2,400 x 1,500
			2,700 x 1,500
RESTOVER® light	2.75	± 0.25	1,000 x 1,500
			1,600 x 1,500
			2,100 x 1,500
	4.0	± 0.25	2,400 x 1,500
			2,100 x 1,500
			2,700 x 1,500
RESTOVER® plus	2.95	± 0.35	1,000 x 1,500
			1,600 x 1,500
			2,100 x 1,500
TIKANA®	4.0	± 0.25	2,100 x 1,500
			2,400 x 1,500
			2,700 x 1,500
	6.0	± 0.50	2,100 x 1,500
			2,400 x 1,500
			2,700 x 1,500

* Other dimensions on request.

SCHOTT Restoration glass GOETHEGLAS, RESTOVER®, TIKANA®

Technical data sheet

GOETHEGLAS

GOETHEGLAS is a colorless, drawn glass with the distinctive, irregular window glass surface typical of the 18th and 19th centuries. It is also suitable as exterior protective glass, e.g. to protect valuable lead glazing from the impact of the weather and the environment.

RESTOVER®

RESTOVER® resembles window glass manufactured around the turn of the last century. Its low thickness facilitates installation in historical window frames and profiles. RESTOVER® light and RESTOVER® plus can provide a less or more textured surface variant resembling traditional blown glass depending on individual requirements.

TIKANA®

TIKANA® is particularly suitable for buildings in the Bauhaus style. Its slightly irregular surface blends harmoniously into classical modernist buildings. Like the other SCHOTT restoration glass, TIKANA® enables an historical look to be integrated into state-of-the-art structural features.



Babelsberg Palace, Babelsberg, Germany



German Historical Museum, Berlin, Germany



Maggi-Areal, Kemptthal, Switzerland

